

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022552442](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: 2.54mm Pitch SL Crimp Housing, Dual Row, Version B, Polarized, 44 Circuits, Black

Documents:
[3D Model](#) [Product Specification PS-70400-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-70450-100-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Test Summary TS-70058-001-001 \(PDF\)](#)
[Product Specification PS-70058-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [70450](#)
Application Signal, Wire-to-Board
Comments Version B
Overview [SL Modular Connectors](#)
Product Name SL
Taxonomy Connector Housings
UPC 800754249447

Physical
Breakaway No
Circuits (maximum) 44
Color - Resin Black
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Material - Resin Polyester
Net Weight 3.770/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Stackable No
Temperature Range - Operating -40° to +105°C

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 704500070

Reference - Drawing Numbers
Packaging Specification PK-70450-100-001
Product Specification PS-70058-001, PS-70400-001
Sales Drawing SD-70450-0050-0075-001
Test Summary TS-70058-001-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[70450 Series](#)

Mates With
C-Grid Right-Angle Header [70229](#) , [70247](#) .
C-Grid Vertical Breakaway Header [70280](#) .
C-Grid Vertical Header [70246](#)

Use With
[70058](#) , [71851](#)