

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026033181

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, 18 Circuits, Natural



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-40-02-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
General	
Product Family	Crimp Housings
Series	6442
Application	Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
Taxonomy	Connector Housings
UPC	800753627055
Physical	
Circuits (maximum)	18
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	4.680/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Stackable	No
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	6442-18-Z
Reference - Drawing Numbers	
Product Specification	PS-40-02-001
Sales Drawing	SD-6442-001, SD-6442-002, SD-6442-003

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

6442 Series

Mates With

Molex 3.96mm pitch KK headers

Use With

MarKK Crimp Terminals [45570](#)
KK Trifurcon Crimp Terminals [6838](#) , [7258](#)
L1NK 396 Pre-Crimped Lead [797582145](#) , [797582146](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION