

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050579003

Status:

Active

Overview:

SL Modular Connectors

Description:

SL Crimp Housing, Single Row, Version A, Non-polarized, 3 Circuits, Black

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-71851-001 (PDF)

Packaging Specification PK-70066-100-001 (PDF)

Test Summary TS-70058-001-001 (PDF)

RoHS Certificate of Compliance (PDF)



Series image - Reference only

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

Taxonomy

UPC

Crimp Housings

70066

Signal, Wire-to-Board

Version A

SL Modular Connectors

SL

Connector Housings

800753578173

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

3

Black

94V-0

Receptacle

No

None

No

Polyester Alloy

0.022/g

1

Bag

No

2.54mm

Yes

-40° to +105°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

70066-0002

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

Test Summary

PK-70066-100-001

PS-70058-001, PS-70400-001, PS-71851-001

SD-70066-0001-0024-001

TS-70058-001-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

70066 Series

Mates With

42375 , 42377 , 70280 , 70287 , 71308 , 70543 , 70553

Use With

SL Crimp Terminal 70058 , 71851

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION