

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050579207

Status:

Active

Overview:

SL Modular Connectors

Description:

SL Crimp Housing, Single Row, Version C, Front Ribs, 7 Circuits, Black

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-71851-001 (PDF)

Packaging Specification PK-70066-100-001 (PDF)

Test Summary TS-70058-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA	LR19980	
UL	E29179	
General		
Product Family	Crimp Housings	
Series	70066	
Application	Signal, Wire-to-Board	
Comments	Version C	
Overview	SL Modular Connectors	
Product Name	SL	
Taxonomy	Connector Housings	
UPC	800753512191	
Physical		
Circuits (maximum)	7	
Color - Resin	Black	
Flammability	94V-0	
Gender	Receptacle	
Glow-Wire Capable	No	
Keying to Mating Part	Yes	
Lock to Mating Part	No	
Material - Resin	Polyester Alloy	
Net Weight	0.051/g	
Number of Rows	1	
Packaging Type	Bag	
Panel Mount	No	
Pitch - Mating Interface	2.54mm	
Stackable	No	
Temperature Range - Operating	-40° to +105°C	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Engineering Number	70066-0076	
Reference - Drawing Numbers		
Packaging Specification	PK-70066-100-001	
Product Specification	PS-70058-001, PS-70400-001, PS-71851-001	
Sales Drawing	SD-70066-0071-0094-001	
Test Summary	TS-70058-001-001	



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70066 Series

Mates With

70543 , 70545 , 70553 , 70555 , 70541 , 70551 , 70634 , 74099

Use With

SL Crimp Terminal 70058 , 71851

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION