

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190080063**  
**Status:** **Active**  
**Overview:** Standard Quick-Disconnect Terminals  
**Description:** Flag Krimptite Quick Disconnect, Female, for 10-12 (3.30 to 5.00mm<sup>2</sup>) Wire, Tab 6.35 x 0.81mm

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-19902-005-001 (PDF)</a>	



**General**

Product Family	Quick Disconnects
Series	<u>19008</u>
Crimp Quality Equipment	Yes
Insulated	No
Overview	<u>Standard Quick-Disconnect Terminals</u>
Product Name	Krimptite
Taxonomy	Quick Disconnects
Type	Quick Disconnect
UPC	800755046786

**Physical**

Barrel Type	Closed
Gender	Female
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.970/g
Orientation	Flag
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	Per Wire Specification
Termination Interface: Style	Crimp or Compression
Wire Size AWG	10, 12

**Electrical**

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Engineering Number	C-1012
--------------------	--------

**Reference - Drawing Numbers**

Product Specification	PS-19902-005-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19008-010-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

19008 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool Krimptite Quick Disconnects	<u>640031600</u>
Air Powered Tool Head	<u>640071600</u>

This document was generated on 10/13/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**