

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191600024

Status:

Active

Overview:

Splices

Description:

Closed-End Insulated Splice for 8 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-013-001 (PDF)

Application Specification PK-19408-109-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Closed-End Insulated
Taxonomy	Splices
UPC	800753110298
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.230/g
Packaging Type	Carton
Temperature Range - Operating	105°C
Wire Insulation Diameter	12.19mm max.
Wire Size AWG	8
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	NC-8
Reference - Drawing Numbers	
Application Specification	PK-19408-109-001
Product Specification	PS-19902-013-001
Sales Drawing	PS-19160-008-001, SD-19160-001-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19160 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool	640012500
Crimp Head for the AT-200 Pneumatic Hand Tool	640052500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION