

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0345660703](#)
Status: **Active**
Overview: [MX123 Sealed Connection System](#)
Description: 2.54mm Pitch, MX123 Female Receptacle Housing, Keying Option G, Wire Dress Option 0, 80 Circuits, Blue TPA

Documents:

3D Model	Packaging Specification PK-31300-019-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-343 (PDF)
Drawing (PDF)	Test Summary TS-34566-002-001 (PDF)
Product Specification PS-34566-0000-001 (PDF)	Test Summary TS-34566-1546-001 (PDF)
Application Specification AS-34566-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	34566
Application	Automotive, Power, Wire-to-Board
Comments	See Sales Drawing for number of Open Circuits, See Sales Drawing for number of Open Circuits
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	822350369312

Physical

Circuits (maximum)	80
Circuits Detail	80
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	51.245/g
Number of Rows	4
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	11.0A, 25.0A
-------------------------------	--------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34566-001-001
Packaging Specification	PK-31300-019-001, PK-31300-343
Product Specification	PS-34566-0000-001
Sales Drawing	12642695-001, 12672833-001, 345660001-SD-000, SD-34566-001-000
Test Summary	TS-34566-002-001, TS-34566-1546-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34566 Series](#)

Mates With

MX123 Header [31386](#) , [31387](#)

Use With

MX64 Female Terminals [33467](#) (AWG, Gold)
MX64 Female Terminals [34736](#) (AWG, Silver)
MX64 Female Terminals [34736](#) (ISO, Silver)

This document was generated on 12/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION