

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391001812

Status:

Active

Overview:

Eurostyle Two-Screw Barrier Strips

Description:

8.00mm Pitch Beau Eurostyle Two-Screw Terminal Strips, 12 Circuits

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	39100
Application	Wire-to-Wire
Component Type	One Piece
Overview	Eurostyle Two-Screw Barrier Strips
Product Name	Eurostyle Two Screw
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	78172545130
Physical	
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	White
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Stainless Steel
Material - Resin	Nylon
Net Weight	32.250/g
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Panel Mount	Mounting Holes Between Circuit
Pitch - Mating Interface	8.00mm
Pitch - Termination Interface	8.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	12, 14, 16, 18, 20, 22
Electrical	
Current - Maximum per Contact	20.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	M800-01-12-5-M1
Reference - Drawing Numbers	
Sales Drawing	SD-39100-011-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION