

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395332004](#)
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 5.08mm Pitch Eurostyle Vertical Plug, Rear Wire Entry, 4 Circuits

Documents:

| | |
|--------------------------------|--|
| 3D Model (PDF) | Product Specification PS-39500-001-001 (PDF) |
| 3D Model | RoHS Certificate of Compliance (PDF) |
| Drawing (PDF) | |

Agency Certification

UL E48521

General

| | |
|----------------|---|
| Product Family | Terminal Blocks |
| Series | 39533 |
| Application | N/A |
| Comments | Rear Wire Entry |
| Component Type | Plug |
| Overview | Eurostyle Terminal Blocks |
| Product Name | ESE, Eurostyle Pluggable |
| Taxonomy | Terminal Blocks and Barrier St |
| Type | Euro Block |
| UPC | 822350523158 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (Loaded) | 4 |
| Entry Angle | Horizontal |
| Lock to Mating Part | Yes |
| Number of Rows | 1 |
| Orientation | Vertical |
| Panel Mount | No |
| Pitch - Mating Interface | 5.08mm |
| Pitch - Termination Interface | 5.08mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm ² | 0.13-3.31 |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 18.0A |
| Voltage - Maximum | 300V |

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------------------------|
| Product Specification | PS-39500-001-001 |
| Sales Drawing | SD-39533-002-001, SD-39533-002-002 |



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[39533](#) Series

Mates With

[39531](#) Vertical PCB Header, [39532](#) Horizontal PCB Header, Most 5.08mm Pitch Industry Standard PCB Headers, [39538](#) Dual Level Header, Open Ends