

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0457501212](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: [Mini-Fit Plus Crimp Terminal, 18-20 AWG, Bag, Copper \(Cu\) Alloy, Gold \(Au\) Selective](#)

Documents:

[Drawing \(PDF\)](#) [Test Summary 457500003-TS-000 \(PDF\)](#)
[Product Specification PS-45750-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-5556-003-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	45750
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current derating information. Series 45750 is Hot-Swappable
	Yes
Crimp Quality Equipment Overview	Mini-Fit Family Power Connectors
Packaging Alternative	457501211 (Reel)
Product Name	Mini-Fit Plus
Taxonomy	Crimp Terminals
UPC	822350286060

Physical

Durability (mating cycles max)	250
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.148/g
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	18, 20
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-5556-003-001
Product Specification	PS-45750-001-001
Sales Drawing	SD-45750-001-001
Test Summary	457500003-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[45750 Series](#)

Use With

[5557](#) Mini-Fit Jr., [30067](#) Mini-Fit TPA, [42474](#) Mini-Fit BMI Panel Mount, [43760](#) Mini-Fit BMI, [44516](#) Mini-Fit BMI Panel Mount Slide-N-Lock

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Mini-Fit Jr. Terminals PremiumGrade Hand	11030044
Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 18-24 AWG	638190901

This document was generated on 10/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION