

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638118700](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 22-24 AWG and 32-36 AWG

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Field Repair, See Tooling Specification (PDF) Above; Type: 4D
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	PremiumGrade
Taxonomy	Crimp Presses and Crimp Hand T
Tool Type	Hand Crimp Tool
UPC	800756875354
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 332.600/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
 ATS-638118700-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

Loose Piece Terminals

**Application Tooling** | **FAQ**

Description	Product #
SL Crimp Terminal, Series 70058, Female, 32-36 AWG, with 0.38µm Selective Gold (Au) Plated Contact, Reel	<a href="#">16020074</a>
SL Crimp Terminal, Series 70021, Male, with 0.38µm Selective Gold (Au) Plated Contact, 22-24 AWG, Reel	<a href="#">16020081</a>
SL Crimp Terminal, Series 70058, Female, 32-36 AWG, with 0.76µm	<a href="#">16020085</a>

Selective Gold (Au)  
Plated Contact, Reel  
SL Crimp Terminal, 16020086  
Series 70058,  
Female, 22-24 AWG,  
with Tin (Sn) Plated  
Contact, Reel  
SL Crimp Terminal, 16020087  
Series 70058,  
Female, 22-24  
AWG, with 0.38µm  
Selective Gold (Au)  
Plated Contact, Reel  
SL Crimp Terminal, 16020088  
Series 70058,  
Female, 22-24  
AWG, with 0.76µm  
Selective Gold (Au)  
Plated Contact, Reel  
SL Crimp Terminal, 16020101  
Series 70058,  
Female, 32-36  
AWG, with 0.76µm  
Selective Gold (Au)  
Plated Contact, Bag  
SL Crimp Terminal, 16020102  
Series 70058,  
Female, 22-24 AWG,  
with Tin (Sn) Plated  
Contact, Bag  
SL Crimp Terminal, 16020103  
Series 70058,  
Female, 22-24  
AWG, with 0.38µm  
Selective Gold (Au)  
Plated Contact, Bag  
SL Crimp Terminal, 16020104  
Series 70058,  
Female, 22-24  
AWG, with 0.76µm  
Selective Gold (Au)  
Plated Contact, Bag  
SL Crimp Terminal, 16020107  
Series 70021, Male,  
with Tin (Sn) Plated  
Contact, 22-24 AWG,  
Reel  
SL Crimp Terminal, 16020114  
Series 70021, Male,  
with Tin (Sn) Plated  
Contact, 22-24 AWG,  
Bag  
SL Crimp Terminal, 16020115  
Series 70021,  
Male, with 0.38µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Bag  
SL Crimp Terminal, 16020116  
Series 70021,  
Male, with 0.76µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Reel

SL Crimp Terminal, [16020117](#)  
Series 70021,  
Male, with 0.76µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Bag  
SL Crimp Terminal, [16021110](#)  
Series 71851,  
Female, with Tin  
(Sn) Plated Contact,  
22-24 AWG, Reel  
SL Crimp Terminal, [16021111](#)  
Series 71851,  
Female, with 0.76µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Reel  
SL Crimp Terminal, [16021114](#)  
Series 71851,  
Female, with Tin  
(Sn) Plated Contact,  
22-24 AWG, Bag  
SL Crimp Terminal, [16021115](#)  
Series 71851,  
Female, with 0.76µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Bag  
SL Crimp Terminal, [16021124](#)  
Series 71851,  
Female, with 0.38µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Reel  
SL Crimp Terminal, [16021125](#)  
Series 71851,  
Female, with 0.38µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Bag  
SL Crimp Terminal, [700210081](#)  
Series 70021,  
Male, with 0.38µm  
Selective Gold (Au)  
Plated Contact,  
22-24 AWG, Reel  
SL Crimp Terminal, [700584086](#)  
Series 70058,  
Female, 22-24 AWG,  
with Tin (Sn) Plated  
Contact, Unplated  
Edges, Reel

This document was generated on 10/12/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**