

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638121100](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Continuity Test Pen Assembly

Documents:

Application Specification AS-34853-001-001 (PDF)	Application Specification AS-560065-002-FR-001 (PDF)
Application Specification AS-34853-001-CH-001 (PDF)	Application Specification AS-98420-003-001 (PDF)
Application Specification AS-34853-001-FR-001 (PDF)	Application Specification AS-98420-003-CH-001 (PDF)
Application Specification AS-560065-002-001 (PDF)	Application Specification AS-98420-003-FR-001 (PDF)
Application Specification AS-560065-002-CH-001 (PDF)	RoHS Certificate of Compliance (PDF)


General

Product Family	Application Tooling
Series	207124
Comments	See Tooling Specification (PDF) Above
Function	Tester
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	N/A
Taxonomy	Application Tooling Accessorie
Tool Type	Crimp Quality Equipment
UPC	884982723955
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Specification	AS-34853-001-001, AS-34853-001-CH-001, AS-34853-001-FR-001, AS-560065-002-001, AS-560065-002-CH-001, AS-560065-002-FR-001, AS-98420-003-001, AS-98420-003-CH-001, AS-98420-003-FR-001
Application Tooling Documents	ATS-638121100-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207124 Series](#)

Use With

CMC Sealed, Hybrid, Modular Connectors and Headers [560065](#) , [64318](#) , [64319](#) , [64320](#) , [64326](#)

Application Tooling | FAQ

Description	Product #
-------------	-----------

.635mm, 1.50mm, 2.80mm, Power CMC Receptacle, 28 Circuits, Left Wire Output, Black Coding, Mat Sealed	643181011
---	---------------------------

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left Wire Output, Gray Coding, Mat Sealed	643181018
---	---------------------------

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	643181019
--	---------------------------

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

.635mm, 1.50mm, 2.80mm, Power CMC Connector, 28 Circuits, Left	
--	--

Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643183011
2.80mm, Power
CMC Connector,
28 Circuits, Right
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643183018
2.80mm, Power
CMC Connector, 28
Circuits, Right Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643183019
2.80mm, Power
CMC Connector,
28 Circuits, Right
Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643191211
CMC Receptacle,
32 Circuits, Left
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643191216
CMC Receptacle, 32
Circuits, Left Wire
Output, Blue Coding,
Mat Sealed
.635mm, 1.50mm, 643191218
CMC Receptacle, 32
Circuits, Left Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643191219
CMC Receptacle,
32 Circuits, Left
Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643192211
CMC Receptacle,
24 Circuits, Left
Wire Output, Black
Coding, Mat Sealed,
Row 1 Closed
.635mm, 1.50mm, 643193211
CMC Receptacle,
32 Circuits, Right
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643193216
CMC Receptacle, 32
Circuits, Right Wire
Output, Blue Coding,
Mat Sealed
.635mm, 1.50mm, 643193218
CMC Receptacle, 32
Circuits, Right Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643193219
CMC Receptacle,
32 Circuits, Right

Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643194211
CMC Receptacle,
24 Circuits, Right
Wire Output, Black
Coding, Mat Sealed,
Row 1 Closed
.635mm, 1.50mm, 643201311
CMC Receptacle,
48 Circuits, Left
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643201315
CMC Receptacle,
48 Circuits, Left
Wire Output, Green
Coding, Mat Sealed
.635mm, 1.50mm, 643201318
CMC Receptacle, 48
Circuits, Left Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643201319
CMC Receptacle,
48 Circuits, Left
Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643202311
CMC Receptacle,
36 Circuits, Left
Wire Output, Black
Coding, Mat Sealed,
Row 1 Closed
.635mm, 1.50mm, 643202319
CMC Receptacle,
36 Circuits, Left
Wire Output, Brown
Coding, Mat Sealed,
Row 1 Closed
.635mm, 1.50mm, 643203311
CMC Receptacle,
48 Circuits, Right
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643203315
CMC Receptacle,
48 Circuits, Right
Wire Output, Green
Coding, Mat Sealed
.635mm, 1.50mm, 643203318
CMC Receptacle, 48
Circuits, Right Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643203319
CMC Receptacle,
48 Circuits, Right
Wire Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643204311
CMC Receptacle,
36 Circuits, Right
Wire Output, Black

Coding, Mat Sealed,
Row 1 closed
.635mm, 1.50mm, 643204319
CMC Receptacle,
36 Circuits, Right
Wire Output, Brown
Coding, Mat Sealed,
Row 1 closed
.635mm, 1.50mm, 643211011
2.80mm, CMC
Receptacle, 53
Circuits, Left Wire
Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643211018
2.80mm, CMC
Receptacle, 53
Circuits, Left Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643211019
2.80mm, CMC
Receptacle, 53
Circuits, Left Wire
Output, Brown
Coding, Mat Sealed
.635mm, 1.50mm, 643212011
2.80mm, CMC
Receptacle, 53
Circuits, Right
Wire Output, Black
Coding, Mat Sealed
.635mm, 1.50mm, 643212018
2.80mm, CMC
Receptacle, 53
Circuits, Right Wire
Output, Gray Coding,
Mat Sealed
.635mm, 1.50mm, 643212019
2.80mm, CMC
Receptacle, 53
Circuits, Right Wire
Output, Brown
Coding, Mat Sealed

This document was generated on 10/10/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION