

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0638194800**
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Tool for 1.20mm Crimp Terminals, 28 AWG Wire for Reeled Product

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|--------------------------------|---|
| Product Family | Application Tooling |
| Series | 207129 |
| Comments | See Tooling Specification (PDF) Above. Type: 7 |
| Function | Crimp |
| Geographic Area | Global |
| Level of Automation | Manual |
| More Detailed Tech Information | applicationtooling@molex.com |
| Overview | Application Tooling |
| Product Name | N/A |
| Tool Type | Hand Crimp Tool |
| UPC | 883906460273 |
| Warranty Disclaimer | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

Physical

Net Weight 610.110/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents
ATS-638194800, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

[78172](#) Pico-Ezmate Wire-to-Board Crimp Terminals, 28 AWG

Application Tooling | FAQ
Description **Product #**

Pico-EZmate Female [781720410](#)
Crimp Terminal, Gold

(Au) over Nickel
Plating 0.10µm,
28-30 AWG, Reel

Pico-EZmate Female [781720411](#)
Crimp Terminal, Gold

(Au) over Nickel
Plating 0.10µm,
28-30 AWG, Reel