

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0638233270

Status:

Active

Overview:

Application Tooling

Description:

Modular Crimp Head for the Battery 638160200 and Air 638160100 Tools

Replacement Part Number :

http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=0638233200638233200

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207129
Comments	See Tooling Specification (PDF) Above; Modular Crimp Heads are not sold separately; the complete hand tool needs to be ordered to obtain a Modular Crimp Head 638233200; Type: TOOL KIT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Replacement Part Number	638233200
Taxonomy	Crimp Presses and Crimp Hand T
Tool Type	Hand Crimp Tool
UPC	884982366480
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Reference - Drawing Numbers	
Application Tooling Documents	ATS-6382332HM-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207129 Series

Application Tooling Description	FAQ Product #
Sabre Crimp Terminal, Male, 14-16 AWG or Double 18+20 AWG, 3.60mm Max. Insulation Diameter, Reel Packaged, Unplated, Brass Contact	431782001
Sabre Crimp Terminal, Male, 14-16 AWG or Double 18+20 AWG, 3.60mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact	431782002
Sabre Crimp Terminal, Male,	431786002

14-16 AWG or
Double 18+20
AWG, 3.60mm
Insulation Diameter,
Reel Packaged,
Tin (Sn) Plated
Brass Contact, Last-
Make Wipe Length,
Complies with
UL1977 Finger Proof
Access Requirement

This document was generated on 10/08/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION