

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0639023400](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** FineAdjust Applicator for Mega-Fit Female Terminals

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207127</a>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	FineAdjust
Taxonomy	Applicators and Crimp Modules
Tool Type	Applicator
UPC	887191147888
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 4672.002/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-639023400-001, TM-638000029-001, TM-638004900-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207127](#) Series

**Use With**

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

**Application Tooling Description**

**FAQ Product #**

Mega-Fit Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 12 AWG, Reel	<a href="#">1720630312</a>
Mega-Fit Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 12 AWG, Reel	<a href="#">1720631312</a>
Mega-Fit Crimp Terminal, Female, Tin (Sn) Plating, 12 AWG, Reel	<a href="#">768230322</a>

This document was generated on 10/12/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**