

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0847330004**  
**Status:** **Active**  
**Overview:** Sealed Industrial USB Solutions  
**Description:** Sealed Industrial USB 3.0 Type A Receptacle-to-USB Type A Plug Dual-Ended Cordset, 0.81m Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-84733-001-001 \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<u>84733</u>
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-A
Overview	<u>Sealed Industrial USB Solutions</u>
Product Name	Industrial USB
Taxonomy	I/O Cable Assemblies
UPC	887191633206

**Physical**

Cable Length	0.81m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Male
Material - Resin	PVC
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Size AWG	N/A
Wire/Cable Type	USB

**Electrical**

Current - Maximum per Contact	1.0A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-84733-001-001
Sales Drawing	SD-84733-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000409978\_00\_000.pdf

CER\_4000410292\_00\_000.pdf

**Search Parts in this Series**

[84733 Series](#)