

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000024](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Metal Cable Gland - 5 Bar, for 6.00-14.00mm Cable, M20x1.5 Thread

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Taxonomy	Heavy-Duty Cable Glands
UPC	887191822563

Physical

Cable Diameter	6.00-14.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	35.000/g
Packaging Type	Bag
Panel Cutout Diameter	20.50mm
Temperature Range - Operating	-40° to +125°C
Thread Size	M20x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Material Info

Engineering Number 7000.6831.0

Reference - Drawing Numbers

Sales Drawing 936000024-000



EU ELV

Compliant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Compliant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

93600 Series

Use With

Industrial connector hoods and housings