

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000042](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Metal Cable Gland, with Washer and Gaskets, Pg21 Thread

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 10.00, 13.00, 16.00, and 19.00mm internal diameters.
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Cable Glands
Product Name	GWconnect
Taxonomy	Heavy-Duty Cable Glands
UPC	887191826141
Physical	
Cable Diameter	9.50-18.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	35.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg21
Thread Type	(Pg)
Material Info	
Engineering Number	7000.6844.0



EU ELV
Compliant

EU RoHS
Compliant with Exemption 6(c)
REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead
Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Compliant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series
[93600 Series](#)

Use With
Enclosures Size A and B metal type