

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000046](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Metal Cable Gland, with Washer and Gaskets, M20x1.5 Thread

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 4.00, 7.00, 10.00, and 13.00mm internal diameters.
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Cable Glands
Product Name	GWconnect
Taxonomy	Heavy-Duty Cable Glands
UPC	887191826189
Physical	
Cable Diameter	3.50-12.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	21.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	M20x1.5
Thread Type	(M) Metric
Material Info	
Engineering Number	7000.6848.0



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

[93600 Series](#)

Use With

Enclosures Size A and B metal type