

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010145

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Screw Terminal Insert, Female, 16-Pole, 16A, Numbered 17-32, with Wire Protection, Silver (Ag) Plated Contacts, Size 16A «66x16»

Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Component Size		16A «66X16»
Component Type		Inserts - Screw Terminal
Insert Series		S-A
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Heavy Duty Connectors
Product Name		GWconnect
Standard		CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
Taxonomy		
UPC		Heavy-Duty Connectors 887191873138
Physical		
Durability (mating cycles max)		500
Flammability		UL 94V-0
Gender		Female
Insert Color		Grey
Material - Contact		Copper Alloy
Material - Insert		Polycarbonate
Material - Plating		Silver
Net Weight		66.000/g
Number of Rows		2
Packaging Type		Bag
Polarized to Mating Part		Yes
Poles		16
Stripping Length		7.00mm
Temperature Range - Operating		-40° to +125°C
Tightening Test Torque		0.50 Nm
Wire Size AWG		14-20
Wire Size mm²		0.50-2.50
Electrical		
Current - Maximum per Contact		16.0A
Voltage - Maximum		250V
Wire Protection		Yes
Material Info		
Engineering Number		7216.4403.0



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93601 Series

Mates With

936010149 Female Screw Terminal Insert

Use With

Size 16A «66x16» Hoods and Housings

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION