

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010171

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 16A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 0.14-0.37mm² (26-22 AWG), 100 per Bag



Documents:

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		256883
UL		E249674
General		
Product Family		Industrial Connectors / Enclosures
Series		93601
Contact Type		Turned Crimp
Overview		GWconnect Heavy Duty Connectors (HDC)
Product Category		Contacts
Product Name		GWconnect
Taxonomy		Heavy-Duty Contacts
UPC		887191874395
Physical		
Gender		Female
Material - Contact		Copper Alloy
Material - Plating		Silver
Net Weight		1.400/g
Number of Grooves		0
Packaging Type		Bag
Stripping Length		7.50mm
Wire Size AWG		22-26
Wire Size mm²		0.14-0.37
Electrical		
Current - Maximum per Contact		16.0A
Material Info		
Engineering Number		7300.6240.0

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

Green Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

93601 Series

Mates With

93601 Male Turned Crimp Contact

Use With

S-AC, S-EC, S-EE, S-EEE, S-EHV,S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION