

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010247](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect Screw Terminal Insert, Male, 4-Pole-80A without Wire Protection and 8-Pole-16A with Wire Protection, Silver (Ag) Plated Contacts, Size 24B «104x27»

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
 UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Component Size 24B «104X27»  
 Component Type Inserts - Screw Terminal  
 Insert Series S-K4/8  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977  
 Taxonomy Heavy-Duty Connectors  
 UPC 887191879055

**Physical**


Durability (mating cycles max) 500  
 Flammability UL 94V-0  
 Gender Male  
 Insert Color Grey  
 Material - Contact Copper Alloy  
 Material - Insert Polycarbonate  
 Material - Plating Silver  
 Net Weight 145.000/g  
 Number of Rows 2  
 Packaging Type Bag  
 Polarized to Mating Part Yes  
 Poles 12  
 Stripping Length 14.00mm, 7.00mm  
 Temperature Range - Operating -40° to +125°C  
 Tightening Test Torque 0.50 Nm, 2.50 Nm  
 Wire Size AWG 14-20, 5-16

**Electrical**

Voltage EN 61984: 500V 6kV 3, UL/CSA: 600V  
 Working Current 80A/16A

**Material Info**

Engineering Number 7312.6143.0



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93601](#) Series

**Mates With**

[936010245](#) Female Screw Terminal Insert

**Use With**

Size 24B «104x27» Hoods and Housings