

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010412

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Turned Crimp Contact for 40A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 6.00mm² (10 AWG), 100 per Bag

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 936010406-S00 (PDF)	

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
Taxonomy	Heavy-Duty Contacts
UPC	887191888705
Physical	
Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	3.000/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	9.60mm
Wire Size AWG	10
Wire Size mm²	6.00
Electrical	
Current - Maximum per Contact	40.0A
Material Info	
Engineering Number	7600.5703.0
Reference - Drawing Numbers	
Product Specification	936010406-S00
Sales Drawing	936010412-000



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Reviewed
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000400719_00_000.pdf

Search Parts in this Series
93601 Series
Mates With
93601 Male Turned Crimp Contact
Use With
S-K, S-Q, S-QD, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION