

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011604](#)
Status: **Active**
Overview:
Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 10B «57x27», Pg21 Thread, High Construction, Grey

Agency Certification

| | |
|-----|---------|
| CSA | 256883 |
| UL | E249674 |

General

| | |
|------------------|---------------------------------------------------------|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93601 |
| Component Size | 10B «57X27» |
| Component Type | Single Lever Hood |
| IP Rating | IP66 |
| Overview | hdc_heavy_duty_connectors |
| Product Category | Heavy Duty Connectors |
| Product Name | GWconnect |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Taxonomy | Heavy-Duty Connectors |
| Type | STD |
| UPC | 887191836591 |

Physical

| | |
|---------------------|-------------------|
| Entry Location | Top |
| Hood Coating | Polyester Powder |
| Hood Color | GREY RAL 7037 |
| Lock to Mating Part | Yes |
| Material - Hood | Die-cast Aluminum |
| Material - Peg | Stainless Steel |
| Net Weight | 194.000/g |
| Number of Pegs | 2 |
| Packaging Type | Bag |
| Thread Size | Pg21 |
| Thread Type | (Pg) |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 7810.6429.5 |
|--------------------|-------------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 936011637-000 |
|---------------|---------------|

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of
Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400719_00_000.pdf

Search Parts in this Series

[93601 Series](#)

Use With

Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts