

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936011797

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Cover, Die-cast Aluminum, with 2 Levers, with Gasket, Size 10B «57x27», Grey

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| Documents:                    |                                                      |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

|                               |                                                         |
|-------------------------------|---------------------------------------------------------|
| Agency Certification          |                                                         |
| CSA                           | 256883                                                  |
| UL                            | E249674                                                 |
| General                       |                                                         |
| Product Family                | Industrial Connectors / Enclosures                      |
| Series                        | 93601                                                   |
| Comments                      | With nylon wire tether line.                            |
| Component Size                | 10B «57X27»                                             |
| Component Type                | Cover                                                   |
| IP Rating                     | IP66                                                    |
| Overview                      | GWconnect Heavy Duty Connectors (HDC)                   |
| Product Category              | Heavy Duty Connectors                                   |
| Product Name                  | GWconnect                                               |
| Standard                      | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Taxonomy                      |                                                         |
| Type                          | Heavy-Duty Connectors                                   |
| UPC                           | STD<br>887191849829                                     |
| Physical                      |                                                         |
| Cover Coating                 | Polyester Powder                                        |
| Cover Color                   | Grey RAL 7037                                           |
| Lock to Mating Part           | Yes                                                     |
| Material - Cover              | Die-cast Aluminum                                       |
| Material - Gasket             | NBR                                                     |
| Material - Lever              | Galvanized Steel                                        |
| Net Weight                    | 121.000/g                                               |
| Number of Levers              | 2                                                       |
| Packaging Type                | Bag                                                     |
| Temperature Range - Operating | -40° to +125°C                                          |
| Thread Size                   | N/A                                                     |
| Thread Type                   | N/A                                                     |
| Electrical                    |                                                         |
| Voltage - Maximum             | 500V                                                    |
| Material Info                 |                                                         |
| Engineering Number            | 7810.6809.0                                             |
| Reference - Drawing Numbers   |                                                         |
| Sales Drawing                 | 936011797-000                                           |



|                                                               |                           |
|---------------------------------------------------------------|---------------------------|
| EU ELV                                                        |                           |
| Not Relevant                                                  |                           |
| EU RoHS                                                       | China RoHS                |
| Compliant                                                     |                           |
| REACH SVHC                                                    |                           |
| Not Contained Per - ED/71/2019 (16 July 2019)                 |                           |
| Halogen-Free                                                  |                           |
| Status                                                        |                           |
| Not Reviewed                                                  |                           |
| For more information, please visit <a href="#">Contact US</a> |                           |
| China ROHS                                                    | Green Image               |
| ELV                                                           | Not Relevant              |
| RoHS Phthalates                                               | Not Contained             |
| ZZCERT_CE - Declaration of Conformity                         | CER_4000400719_00_000.pdf |

|                                       |
|---------------------------------------|
| Search Parts in this Series           |
| 93601 Series                          |
| Use With                              |
| Size 10B «57x27» Housings with 4 Pegs |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION