

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936012519](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 16B «77x27», Grey, with IP66 - Ribbon Cable Gland, Grey, Cable Size 3.80-9.00mm x 40.00-47.00mm, High Construction

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
 UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Cable Gland Type IP66 - Ribbon Cable  
 Component Size 16B «77X27»  
 Component Type Double Lever Hood  
 IP Rating IP66  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
 Taxonomy Heavy-Duty Connectors  
 Type STD  
 UPC 887191824956

**Physical**

Entry Location Top  
 Flammability UL 94V-0  
 Gland Color Grey RAL 7037  
 Hood Color GREY RAL 7037  
 Lock to Mating Part Yes  
 Material - Cable Gland Polyamide  
 Material - Gasket Silicone  
 Material - Hood Die-cast Aluminum  
 Material - Peg Stainless Steel  
 Net Weight 310.000/g  
 Number of Pegs 4  
 Packaging Type Bag  
 Ribbon Cable Size 3.80-9.00mm X 40.00-47.00mm  
 Temperature Range - Operating -40° to +100°C  
 Waterproof / Dustproof Yes  
 Waterproof / Dustproof Type IP66, IP69

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7816.5367.0



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**China RoHS**

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K,S-M, and S-EHV Inserts and Ribbon Cable