

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936012587

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 16B «77x27», Pg21 Thread, High Construction, Grey

<b>Documents:</b>	
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<b>Agency Certification</b>	
CSA	256883
UL	E249674
<b>General</b>	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Double Lever Hood
IP Rating	IP66
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
<b>Taxonomy</b>	
Type	Heavy-Duty Connectors
UPC	STD 887191835730
<b>Physical</b>	
Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	225.300/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)
<b>Electrical</b>	
Voltage - Maximum	500V
<b>Material Info</b>	
Engineering Number	7816.6423.5
<b>Reference - Drawing Numbers</b>	
Sales Drawing	936012587-001



**EU ELV**  
**Not Relevant**

**EU RoHS**  
**Compliant**  
**REACH SVHC**  
Not Contained Per -  
D(2022)4187-DC (10  
June 2022)  
**Halogen-Free**  
**Status**  
**Low-Halogen**  
For more information, please visit [Contact US](#)

**China RoHS**  
Green Image  
Not Relevant  
Not Contained  
CER\_4000400719\_00\_000.pdf

**Search Parts in this Series**  
93601 Series

**Use With**  
Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION