

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

**Part Number:** 0936012734

**Status:** **Active**

## Overview: GWconnect Heavy Duty Connectors (HDC)

**Description:** GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 16B «77x27», Pg29 Thread, High Construction, Grey

## Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

## Agency Certification

|     |         |
|-----|---------|
| CSA | 256883  |
| UL  | E249674 |

## General

|                  |                                                         |
|------------------|---------------------------------------------------------|
| Product Family   | Industrial Connectors / Enclosures                      |
| Series           | <u>93601</u>                                            |
| Component Size   | 16B «77X27»                                             |
| Component Type   | Single Lever Hood                                       |
| IP Rating        | IP66                                                    |
| Overview         | <u>GWconnect Heavy Duty Connectors (HDC)</u>            |
| Product Category | Heavy Duty Connectors                                   |
| Product Name     | GWconnect                                               |
| Standard         | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Taxonomy         | Heavy-Duty Connectors                                   |
| Type             | STD                                                     |
| UPC              | 887191845326                                            |

## Physical

|                     |                   |
|---------------------|-------------------|
| Entry Location      | Side              |
| Hood Coating        | Polyester Powder  |
| Hood Color          | GREY RAL 7037     |
| Lock to Mating Part | Yes               |
| Material - Hood     | Die-cast Aluminum |
| Material - Peg      | Stainless Steel   |
| Net Weight          | 224.000/g         |
| Number of Pegs      | 2                 |
| Packaging Type      | Bag               |
| Thread Size         | Pg29              |
| Thread Type         | (Pg)              |

## Electrical

|                   |      |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

## Material Info

Engineering Number 7816.6482.5



Series image - Reference only

## EU ELV

**Not Relevant**

## EU RoHS

## Compliant

## REACH SVHC

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

### Halogen-Free

## Status

**Not Reviewed**

For more information, please visit [Contact US](#)

|                   |                             |
|-------------------|-----------------------------|
| China ROHS<br>ELV | Green Image<br>Not Relevant |
|-------------------|-----------------------------|

|                 |               |
|-----------------|---------------|
| RoHS Phthalates | Not Contained |
|-----------------|---------------|

ZZCERT CE - CER 4000400719 00 000.pdf

## Declaration of Conformity

### Search Parts in this Series

## 93601 Series

## Use With

Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**