

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936012868](#)

**Status:** **Active**

**Overview:** GWconnect Heavy Duty Connectors (HDC)

**Description:** GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Double Top Entry, Size 16B «77x27», Pg16x2 Extended Threaded Fitting, Grey, High Construction

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
Series [93601](#)  
Component Size 16B «77X27»  
Component Type Double Lever Hood  
IP Rating IP66  
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
Product Category Heavy Duty Connectors  
Product Name GWconnect  
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
Taxonomy Heavy-Duty Connectors  
Type STD  
UPC 887191854496

**Physical**

Entry Location Top  
Hood Coating Polyester Powder  
Hood Color GREY RAL 7037  
Lock to Mating Part Yes  
Material - Hood Die-cast Aluminum  
Material - Peg Stainless Steel  
Number of Pegs 4  
Packaging Type Bag  
Thread Size Pg16x2  
Thread Type (Pg)

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7816.6621.0



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts