

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013330](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 24B «104x27», Pg29 Thread, High Construction, Grey

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Color - Cable Jacket N/A
 Component Size 24B «104X27»
 Component Type Double Lever Hood
 IP Rating IP66
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Taxonomy Heavy-Duty Connectors
 Type STD
 UPC 887191884578

Physical

Entry Location Side
 Hood Coating Polyester Powder
 Hood Color GREY RAL 7037
 Lock to Mating Part Yes
 Material - Hood Die-cast Aluminum
 Material - Lever Galvanized Steel
 Net Weight 301.000/g
 Number of Levers 2
 Packaging Type Bag
 Thread Size Pg29
 Thread Type (Pg)

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7824.5111.5

Reference - Drawing Numbers

Sales Drawing 936013306-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400780_00_000.pdf

Search Parts in this Series

[93601 Series](#)

Use With

Size 24B «104x27» S-D, S-DD, S-E, S-EE,
 S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M,
 and S-EHV Inserts