This document was generated on 10/26/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936013610

Status: Active

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», M32 Thread, High Construction, Grey

Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Double Lever Hood
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Taxonomy	Heavy-Duty Connectors
Type	STD
UPC	887191848891

Physical

Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	263.120/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M32
Thread Type	(M) Metric

Electrical

Voltage - Maximum	500V

Material Info

Engineering Number	7824.6447.5

Reference - Drawing Numbers

Sales Drawing	936013610-000

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000400780_00_000.pdf

Search Parts in this Series
93601 Series

Use With
Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

This document was generated on 10/26/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION