

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936013849](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Cover, Die-cast Aluminum, with 1 Lever, with Gasket, with Gasket, Size 24B «104x27», Grey

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
 UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Comments With nylon wire tether line.  
 Component Size 24B «104X27»  
 Component Type Cover  
 IP Rating IP66  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
 Taxonomy Heavy-Duty Connectors  
 Type STD  
 UPC 887191865676

**Physical**

Cover Coating Polyester Powder  
 Cover Color Grey RAL 7037  
 Lock to Mating Part Yes  
 Material - Cover Die-cast Aluminum  
 Material - Gasket NBR  
 Material - Lever Galvanized Steel  
 Net Weight 124.800/g  
 Number of Levers 1  
 Packaging Type Bag  
 Thread Size N/A  
 Thread Type N/A

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7824.6821.0



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400780\_00\_000.pdf

**Search Parts in this Series**

[93601](#) Series

**Use With**

Size 24B «104x27» Housings with 2 Pegs