

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936014121

Status: **Active**

Overview: GWconnect Heavy Duty Connectors (HDC)

Description: GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry. Size 32A «66x40». M25 Thread. High Construction. Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	<u>93601</u>
Component Size	32A «66x40»
Component Type	Double Lever Hood
IP Rating	IP66
Overview	<u>GWconnect Heavy Duty Connectors (HDC)</u>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Taxonomy	Heavy-Duty Connectors
Type	STD
UPC	887191882383

Physical

Entry Location	Top
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	267.000/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number 7832.4641.5



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT CE -

Declaration of Conformity

Green Image

Not Relevant

Not Contained

CER 4000400780 00 000.pdf

Search Parts in this Series

93601 Series

Use With

Size 32A «66x40» S-A and S-D Inserts