

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014686](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg16 Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size «32X13»
 Component Type Single Lever Bulkhead Housing
 IP Rating IP66, IP67
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Taxonomy Heavy-Duty Connectors
 Type STD
 UPC 887191842653

Physical

Cable Diameter 8.00-14.00mm
 Entry Location Side
 Flammability UL 94V-0
 Gland Color Black RAL 9005
 Housing Color Black RAL 9005
 Lock to Mating Part Yes
 Material - Cable Gland Polyamide
 Material - Housing Polyamide
 Material - Lever Polyamide
 Mounting Style Bulkhead
 Net Weight 48.000/g
 Number of Levers 1
 Packaging Type Bag
 Thread Size Pg16
 Thread Type (Pg)

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7908.6663.1



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size «32x13» S-QD Inserts