

 [Live Product Chat](#)



Product Highlights:

- Housing
- Preloaded
- Number of Positions = 10
- Housing Type = Receptacle
- Contact Type = Receptacle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings: • RECEPTACLE ASSY, AMPMODU, MASS TERMINATION, DBL ROW... (PDF, English) Catalog Pages/Data Sheets: • None Available Product Specifications: • Connector, AMPMODU, Mass Terminated Standard Pressure (PDF, English) • Interconnection System, AMPMODU MT, Shielding Access... (PDF, English) Application Specifications: • AMPMODU Mass Termination (MT) Interconnection System (PDF, English) Instruction Sheets: • None Available CAD Files: • None Available List all Documents	Additional Information: • Product Line Information Related Products: • Tooling
--	--

Product Type Features: • Product Type = Housing • Number of Positions = 10 • Mating Connector Lock = Without • Mating Polarization = Without • Wire Insulation Diameter (mm [In]) = 1.27 [0.050] • Keyed = No • Connector Series = MT • Wire Termination Type = Insulation Displacement Crimp (IDC) • Applied Pressure = Standard Mechanical Attachment: • Preloaded = Yes Termination Related Features: • Solder Tail Contact Plating = Tin-Lead Body Related Features: • Housing Type = Receptacle • Number of Rows = Dual • Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100] • Wire Range (mm [AWG]) = 0.12-0.40² [26-22]	Contact Related Features: • Contact Type = Receptacle • Contact Mating Area Plating Material = Gold (50) • Contact Material = Phosphor Bronze Housing Related Features: • Housing Color = Black • Housing Material = Thermoplastic Industry Standards: • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not relevant for lead free process Conditions for Usage: • Terminate To = Wire Other: • Brand = AMP
--	--