

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Number of Positions = 15
? Receptacle
? PCB Mount Angle = Right Angle
? Product Series = HD -22
? With Mating Connector Lock

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[RCPT ASM, SZ 1, 15POSN, RT ANG, Front Metal Shell, A...](#) (PDF, English)

? None Available

? None Available

[AMPLIMITE HD -22 Right -Angle Front Metal Shell Connectors](#)
(PDF, English)

? None Available

- ? 2D Drawing (DXF, Version O)
- ? 3D Model (IGES, Version O)
- ? 3D Model (STEP, Version O)

Product Line Information

? Tooling

List all Documents

Product Type Features:

Panel Attachment = Without
Boardlock Hole Diameter (mm [in]) = 3.20
[0.126]
Boardlock Material = Brass
Boardlock Plating = Tin over Nickel

? Grounding Clips = Without

? Termination (Solder) Post Length (mm [in]) = 2.67 [0.105]

? Solder Tail Contact Plating = Tin over Nickel

PCB Retention Method = Boardlock(s)
 ? Insert Material = Copper Alloy
 ? Shell Plating = Nickel

? Contact Mating Area Plating Material = Gold
 ? Flash
 ? Contact Shape = Round
 ? Contact Material = Phosphor Bronze

? Housing Flammability Rating = UL 94V -0

? Housing Material = Thermoplastic

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Application = Standard

? Packaging Method = Tray

? Brand = AMP