

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200740042

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (1/2" - 20 UNF) US Dual Keyway Receptacle, 2 Poles, 1/2" -14 NPT Mounting Threads, Male (Straight) to 22 AWG PVC Leads, 0.305m (1.0') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Receptacles
Series	120074
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (1/2" - 20 UNF)
Taxonomy	Circular Industrial Connectors
Type	Single Ended (pigtail)
UPC	78678822668
Physical	
Coupling Type	External Thread
Gender	Male
Keyway	Dual
Length	0.305m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	125.000/g
Orientation	Straight
Panel Mount	Front
Poles	2
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	22
Wire/Cable Type	Leads, UL 1061
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	7R2006A19A120
Reference - Drawing Numbers	
Sales Drawing	SD-120074-002-001

EU ELV

Not Reviewed

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

ZZCERT_CE - Declaration of Conformity

CER_4000410036_00_000.pdf

ZZCERT_UKCA - Declaration of Conformity

CER_4000410293_00_000.pdf

Search Parts in this Series

120074 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION