

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200750017](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Dual Keyway with PG7 Cable Fitting, Straight Male, 3 Poles, Cable Diameter 3.30-6.60mm

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">120075</a>
Approvals	N/A
IP Rating	IP67
Material - Contact	Brass
Overview	<a href="#">Brad Micro-Change (M12) Connectors</a>
Product Name	Micro-Change (1/2" - 20 UNF)
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	78678830718

**Physical**

Cable Diameter	3.30-6.60mm (.130-.260")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Dual
Material - Connector Body	PA
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	24.040/g
Orientation	Straight
Poles	3
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	18

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC / 300V DC

**Material Info**

Engineering Number	7A3006-31
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	SD-120075-005-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

ZZCERT\_CE -

CER\_4000406200\_00\_000.pdf

Declaration of

Conformity

ZZCERT\_UKCA

CER\_4000410292\_00\_000.pdf

- Declaration of

Conformity

**Search Parts in this Series**

[120075 Series](#)