

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200890033](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) 4 Pole, Male to 2-Female Solid Body Y

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Tees and Splitters
Series	120089
IP Rating	N/A
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Taxonomy	Industrial Tees and Splitters
Type	Splitter - Solid Body
UPC	78678843586

Physical

Color - Cable Jacket	Black
Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	No
Left Trunk Connector	Nano-Change (M8)
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	10.400/g
Poles	4
Right Trunk Connector	Nano-Change (M8)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

Material Info

Engineering Number	080804LMF00000
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-120089-015-001
---------------	-------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410542_00_000.pdf

Search Parts in this Series

[120089 Series](#)