

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080392](#)
Status: **Active**
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 80.0m (262.40') Length, 6.99mm (.275") Diameter, Teal
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=13004803251300480325> (drop-in)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E361772

General

Product Family Industrial Cordsets
 Series [120108](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Performance Category 5e
 Product Name Micro-Change (M12)
 Protocol EtherNet
 Replacement Part Number [1300480325](#) (drop-in)
 Type Double Ended
 UPC 78172543407

Physical

Cable Diameter 6.99mm (.275")
 Cable Length 80.0m (262.40')
 Color - Cable Jacket Teal
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket TPE
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -20°C to +75°C
 Wire Size AWG 24
 Wire/Cable Type TPE

Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V

Material Info

Engineering Number E11A06007M800

Reference - Drawing Numbers

Sales Drawing SD-120108-057

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120108](#) Series

This document was generated on 02/20/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION