

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202330001](#)
Status: **Active**
Overview: Brad M23 Signal and Power Connectors
Description: Brad M23 Power Connector, Straight Female, Crimp Contacts, 6 (5+PE) Poles, Cable Diameter 7.00-12.00mm

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	120233
Application	Power
Comments	Crimp Range 0.75-2.50mm2
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301316

Physical

Cable Diameter	7.00-12.00mm (.276-.472")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	Straight
Poles	6 (5+PE)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	28.0A
Voltage - Maximum	600V

Material Info

Engineering Number	KAP6S00-105
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	SD-120233-001-001
---------------	-------------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120233 Series](#)