

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210230633

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form A-18mm, PG11 Internal Threads, 3 Pole Plus Ground, Black, Nitrile Gasket, Bulk Pack Mounted

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-121023-C81-001 (PDF)

General

Product Family

Field Attachable / Accessories

Series

121023

Form

A - 18mm

IP Rating

IP65, IP67

Material - Contact

Brass

Overview

mPm DIN Valve Connectors

Product Name

mPm

Taxonomy

Circular Industrial Connectors

Type

Field Attachable Connector

UPC

883906249199

Physical

Cable Diameter

N/A

Coupling Type

Internal Thread

Diagnostics / LEDs

No

Diagnostics Port

No

Gender

N/A

Keyway

None

Material - Connector Body

Polypropylene

Material - Coupling Nut

N/A

Material - Plating Mating

Silver

Net Weight

29.489/g

Orientation

90° Angle

Pitch - Mating Interface

18.00mm

Poles

3

Temperature Range - Operating

-40°C to +90°C

Wire Size AWG

N/A

Electrical

Current - Maximum per Contact

16.0A

Voltage - Maximum

250V AC / 300V DC

Material Info

Engineering Number

C81311N21

Reference - Drawing Numbers

Packaging Specification

PK-121023-C81-001

Sales Drawing

SD-121023-008-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121023 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION