

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1210360255

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

Micro-Change (M12) to Brad mPm DIN Form B - 11mm Cordset, C4 Circuit, Yellow LED, 5 Poles, Male (Straight), Black PUR Cable, 1.0m (3.28') Length , 24V



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	121036
Connector End A	Brad mPm DIN B - 11mm
Connector End B	Micro-Change (M12)
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	mPm DIN Valve Connectors
Product Name	Micro-Change (M12), mPm
Protocol	N/A
Region	America, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	883906501655
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	Yellow
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	114.000/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire Size AWG	20
Wire/Cable Type	PUR
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	24V
Material Info	
Engineering Number	F850B0P12M010
Reference - Drawing Numbers	
Sales Drawing	SD-121036-002-001

EU ELV	
Not Relevant	
EU RoHS	
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

121036 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION