

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212020002

Status:

Active

Overview:

mPm DIN Valve Connectors

Description:

mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black, Nitrile Gasket, Bulk Pack, Unmounted

Documents:

Drawing (PDF)

Product Specification PS-121201-001-001 (PDF)

Product Specification STR-1251-001 (PDF)

Packaging Specification PK-121202-C22-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Form

IP Rating

Material - Contact

Overview

Product Name

Taxonomy

Type

UPC

Field Attachable / Accessories

121202

B - 11mm

IP65, IP67

Brass

mPm DIN Valve Connectors

mPm

Circular Industrial Connectors

Field Attachable Connector

883906711504

Physical

Cable Diameter

Coupling Type

Diagnostics / LEDs

Diagnostics Port

Gender

Keyway

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Net Weight

Orientation

Pitch - Mating Interface

Poles

Temperature Range - Operating

Wire Size AWG

N/A

External Thread

No

No

N/A

None

Polyamide

N/A

Silver

19.522/g

90° Angle

11.00mm

2

-40°C to +90°C

N/A

Electrical

Current - Maximum per Contact

Voltage - Maximum

16.0A

250V AC/DC

Material Info

Engineering Number

C22200N0RCN

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-121202-C22-001

PS-121201-001-001, STR-1251-001

SD-121202-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

121202 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION