

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212050001](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C-Micro 9.4mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black, Nitrile Gasket

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121205-C29-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1299-001 \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121205
Form	C - Micro 9.4mm
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	884982268692

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	10.600/g
Orientation	90° Angle
Pitch - Mating Interface	9.40mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	C29200N0T
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121205-C29-001
Product Specification	PS-121201-001-001, STR-1299-001
Sales Drawing	SD-121205-001-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

China RoHS

ELV

50 Image

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[121205 Series](#)