

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212080042](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with A1 Circuit, 115V, Red LED, Transparent, Nitrile Gasket

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121208-S22-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)

General

Product Family Field Attachable / Accessories
 Series [121208](#)
 Form B - 11mm
 IP Rating IP65, IP67
 Material - Contact Brass
 Overview [mPm DIN Valve Connectors](#)
 Product Name mPm
 Taxonomy Circular Industrial Connectors
 Type Field Attachable Connector
 UPC 884982509603

Physical

Cable Diameter N/A
 Coupling Type External Thread
 Diagnostics / LEDs Yes
 Diagnostics Port No
 Gender N/A
 Keyway None
 Material - Connector Body Polyamide
 Material - Coupling Nut N/A
 Material - Plating Mating Silver
 Net Weight 19.489g
 Orientation 90° Angle
 Pitch - Mating Interface 11.00mm
 Poles 2
 Temperature Range - Operating -40°C to +90°C
 Wire Size AWG N/A

Electrical

Current - Maximum per Contact 16.0A
 Voltage - Maximum 115V

Material Info

Engineering Number S22200TA140R

Reference - Drawing Numbers

Packaging Specification PK-121208-S22-001
 Product Specification PS-121201-001-001, STR-1251-001
 Sales Drawing SD-121208-001-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
 Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[121208 Series](#)