

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212100342](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C-8mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED + VDR, Transparent, Profiled NBR Gasket, Bulk Pack, Mounted

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121210-S25-001 \(PDF\)](#)
[Product Specification STR-1299-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121210
Form	C - 8mm
IP Rating	IP67
Material - Contact	Brass
Overview	mPm DIN Valve Connectors
Product Name	mPm
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	884982541856

Physical

Cable Diameter	3.00-5.50mm
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	8.160/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	18

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Material Info

Engineering Number	S25200TC4H2TSN
--------------------	----------------

Reference - Drawing Numbers

Packaging Specification	PK-121210-S25-001
Product Specification	STR-1299-001
Sales Drawing	SD-121210-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[121210 Series](#)