

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130000052](#)  
**Status:** **Active**  
**Overview:** [Brad Quick-Change Connectors](#)  
**Description:** Quick-Change Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 3.66m (12.0') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E46237

**General**

Product Family Industrial Cordsets  
 Series [130000](#)  
 Connector End A Quick-Change  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Quick-Change Connectors](#)  
 Product Name Quick-Change  
 Region America  
 Taxonomy Circular Industrial Cordsets  
 Type Single Ended  
 UPC 78678832356

**Physical**

Cable Diameter 16.63mm (.655")  
 Cable Length 3.66m (12.0')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Female-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket CPE  
 Material - Connector Body TPE  
 Material - Coupling Nut Nylon  
 Material - Plating Mating N/A  
 Net Weight 584.000/g  
 Orientation Straight to Pigtail  
 Poles 3  
 Temperature Range - Operating -20° to +105°C  
 Wire Size AWG 12  
 Wire/Cable Type SOW

**Electrical**

Current - Maximum per Contact 25.0A  
 Voltage - Maximum 600V

**Material Info**

Engineering Number 32356

**Reference - Drawing Numbers**

Sales Drawing 1300000045-000



*Series image - Reference only*

**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant with

Exemption 3

Not Contained

**Search Parts in this Series**

[130000 Series](#)

This document was generated on 09/26/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**