

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300060156

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Single-Ended Cordset, 2 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow PVC Cable, 0.91m (3.0') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	130006
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	N/A
Region	America
Taxonomy	Circular Industrial Cordsets
Type	Single Ended
UPC	78678842956
Physical	
Cable Diameter	9.40mm (.370")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	155.000/g
Orientation	Straight to Pigtail
Poles	2
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	102002A01F030
Reference - Drawing Numbers	
Sales Drawing	SD-130006-002-001



EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000410036_00_000.pdf
ZZCERT_UKCA - Declaration of Conformity	CER_4000410293_00_000.pdf

Search Parts in this Series

130006 Series

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION