

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300250508

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), Gray DeviceNet Thin High Flex Cable, 5.0m (16.40') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Region

Taxonomy

Type

UPC

Industrial Cordsets

130025

Mini-Change

Mini-Change

IP67

Brass

Brad Mini-Change Connectors

DeviceNet Trunk, Mini-Change

Europe

Circular Industrial Cordsets

Double Ended

78678850695

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Net Weight

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

7.62mm (.300")

5.0m (16.40')

Gray

Threaded

Female-Male

Single

No

TPE

TPE

Die-Cast Zinc

Gold

501.219/g

Straight to Straight

5

-20° to +80°C

22

Thin Flex-Rated Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

300V AC/DC

Material Info

Engineering Number

DNDF11A-M050

Reference - Drawing Numbers

Sales Drawing

SD-130025-020-001



EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of Conformity

50 Image

Not Relevant

Not Contained

CER_4000410292_00_000.pdf

Search Parts in this Series

130025 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION